

Garant**Turning insert, medium machining VBMT, HB7020, Size / quantity: 160404/30****Order data**

Order number	GG2636 160404/30
GTIN	4067263095873
Item class	GGN

Technical description

Contents	261232 HB7020
Feed f	0.1 - 0.25 mm/rev.
Cutting speed v_c main application	130 - 280 mm/min
Cutting depth a_p	0.25 - 2.5 mm
Quantity	30
ISO code indexable insert	VBMT160404
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

VB.T 160404 Grade HB7020

261232 HB7020