

Garant**Turning insert, medium machining TCMT, HB7020, Size / quantity: 16T304/30****Order data**

Order number	GG2632 16T304/30
GTIN	4067263095750
Item class	GGN

Technical description

Feed f	0.1 - 0.25 mm/rev.
Contents	260986 HB7020
Cutting depth a_p	0.25 - 4 mm
Cutting speed v_c main application	130 - 280 mm/min
Quantity	30
ISO code indexable insert	TCMT16T304
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

TC.T 16T304 Grade HB7020

260986 HB7020