


**Turning insert, medium machining TCMT, HBT020, Size / quantity: 16T308/30****Order data**

Order number	GG2635 16T308/30
GTIN	4067263095835
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 4 mm
Feed f	0.2 - 0.3 mm/rev.
Contents	261019 HBT020
Cutting speed v_c main application	120 - 240 mm/min
Quantity	30
ISO code indexable insert	TCMT16T308
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

TCMT 16T308 Grade HBT020

261019 HBT020