

**Garant****Turning insert, medium machining VBMT, HB7020, Size / quantity: 160408/50****Order data**

Order number	GG2636 160408/50
GTIN	4067263095903
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.55 - 2.5 mm
Cutting speed $v_c$ main application	130 - 280 mm/min
Feed $f$	0.1 - 0.25 mm/rev.
Contents	261234 HB7020
Quantity	50
ISO code indexable insert	VBMT160408
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

VB.T 160408 Grade HB7020

261234 HB7020