

Garant**Turning insert, medium machining VBMT, HB7020, Size / quantity: 110304/30****Order data**

Order number	GG2636 110304/30
GTIN	4067263095859
Item class	GGN

Technical description

Cutting depth a_p	0.25 - 1.75 mm
Cutting speed v_c main application	130 - 280 mm/min
Feed f	0.1 - 0.25 mm/rev.
Contents	261224 HB7020
Quantity	30
ISO code indexable insert	VBMT110304
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

VB.T 110304 Grade HB7020

261224 HB7020