

Garant**Turning insert, medium machining VCMT, HB7020, Size / quantity: 160404/50****Order data**

Order number	GG2640 160404/50
GTIN	4067263096009
Item class	GGN

Technical description

Cutting speed v_c main application	130 - 280 mm/min
Feed f	0.1 - 0.25 mm/rev.
Cutting depth a_p	0.25 - 2.5 mm
Contents	261458 HB7020
Quantity	50
ISO code indexable insert	VCMT160404
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

VC.T 160404 Grade HB7020

261458 HB7020