

HOLEX**Turning insert, medium machining VBMT, HBT020, Size / quantity: 160408/50**

Order data

Order number	GG2639 160408/50
GTIN	4067263095965
Item class	GGN

Technical description

Feed f	0.2 - 0.3 mm/rev.
Contents	261259 HBT020
Cutting speed v_c main application	120 - 240 mm/min
Cutting depth a_p	0.55 - 2.5 mm
Quantity	50
ISO code indexable insert	VBMT160408
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

VBMT 160408 Grade HBT020

261259 HBT020