

**Turning insert, medium machining VCMT, HBT020, Size / quantity: 160404/50****Order data**

Order number	GG2643 160404/50
GTIN	4067263096061
Item class	GGN

Technical description

Cutting depth a_p	0.25 - 2.5 mm
Contents	261474 HBT020
Feed f	0.2 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 240 mm/min
Quantity	50
ISO code indexable insert	VCMT160404
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

VCMT 160404 Grade HBT020

261474 HBT020