

**Turning insert, medium machining VBMT, HBT020, Size / quantity: 160404/30****Order data**

Order number	GG2639 160404/30
GTIN	4067263095934
Item class	GGN

Technical description

Cutting speed v_c main application	120 - 240 mm/min
Feed f	0.2 - 0.3 mm/rev.
Contents	261257 HBT020
Cutting depth a_p	0.25 - 2.5 mm
Quantity	30
ISO code indexable insert	VBMT160404
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

Accessories

VBMT 160404 Grade HBT020

261257 HBT020