

**Garant****Turning insert, medium machining VCMT, HB7020, Size / quantity: 160404/30****Order data**

Order number	GG2640 160404/30
GTIN	4067263095996
Item class	GGN

**Technical description**

Feed f	0.1 - 0.25 mm/rev.
Cutting speed $v_c$ main application	130 - 280 mm/min
Contents	261458 HB7020
Cutting depth $a_p$	0.25 - 2.5 mm
Quantity	30
ISO code indexable insert	VCMT160404
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

VC.T 160404 Grade HB7020

261458 HB7020