

**Garant****Turning insert, medium machining VCMT, HB7020, Size / quantity: 160408/30****Order data**

Order number	GG2640 160408/30
GTIN	4067263096016
Item class	GGN

**Technical description**

Feed f	0.1 - 0.25 mm/rev.
Cutting speed $v_c$ main application	130 - 280 mm/min
Cutting depth $a_p$	0.55 - 2.5 mm
Contents	261459 HB7020
Quantity	30
ISO code indexable insert	VCMT160408
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

VC.T 160408 Grade HB7020

261459 HB7020