

HOLEX**Turning insert, medium machining DCMT, HBT130, Size / quantity: 11T308/50****Order data**

Order number	GG2651 11T308/50
GTIN	4067263096603
Item class	GGN

Technical description

Feed f	0.2 - 0.3 mm/rev.
Cutting depth a_p	0.55 - 2.75 mm
Cutting speed v_c main application	80 - 135 mm/min
Contents	260508 HBT130
Quantity	50
ISO code indexable insert	DCMT11T308
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

DCMT 11T308 Grade HBT130

260508 HBT130