


**HOLEX**
**HOLEX Pro Inox solid carbide high-performance drill, plain shank DIN 6535 HA, AlTiN, Ø DC m7: 5mm**

**Order data**

Order number	GG2685 5
GTIN	4067263087717
Item class	GGN

**Description**
**Version:**

Efficient drilling especially for use in **stainless and acid-resistant steels**.

Straight main cutting edges with **optimised cutting edge design** for improved chip breaking behaviour. Enlarged flutes for **excellent chip evacuation**. Increased wear resistance due to **improved carbide substrate** and **high temperature resistant coating**.

**Same as number. 122685.**

Form HB available with No. GG 1286 at the same price. Form HB only available from  $\geq \text{Ø } 3 \text{ mm}$ .

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

**Technical description**

Contents	5
Standard	DIN 6537
recommended maximum drilling depth $L_2$	36.5 mm
Overall length $L$	82 mm
Flute length $L_c$	44 mm

Shank $\varnothing D_s$	6 mm
Nominal $\varnothing D_c$	5 mm
Feed $f$ in stainless steel $< 900 \text{ N/mm}^2$	0.07 mm/rev.
Number of cutting edges $Z$	2
Tolerance nominal $\varnothing$	m7
Series	Pro Inox
Coating	AlTiN
Tool material	Solid carbide
Version	6xD
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Colour ring	blue
Type of product	Twist Drill

## User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Alu $> 10\% \text{ Si}$	suitable only under restricted conditions		
Steel $< 500 \text{ N/mm}^2$	suitable		
Steel $< 750 \text{ N/mm}^2$	suitable		
Steel $< 900 \text{ N/mm}^2$	suitable		
Steel $< 1100 \text{ N/mm}^2$	suitable		
INOX $< 900 \text{ N/mm}^2$	suitable		
INOX $> 900 \text{ N/mm}^2$	suitable		
Ti $> 850 \text{ N/mm}^2$	suitable		
wet maximum	suitable		

wet minimum

suitable only under  
restricted conditions

---

## Accessories

HOLEX Pro Inox solid carbide high-performance drill, plain  
shankDIN 6535 HA Ø DC m7 5 mm

122685 5