

**Turning insert, medium machining TCMT, HBT130, Size / quantity: 16T308/30****Order data**

Order number	GG2659 16T308/30
GTIN	4067263096979
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 4 mm
Feed f	0.2 - 0.3 mm/rev.
Contents	261019 HBT130
Cutting speed v_c main application	80 - 135 mm/min
Quantity	30
ISO code indexable insert	TCMT16T308
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

TCMT 16T308 Grade HBT130

261019 HBT130