

Garant**Turning insert, medium machining TCMT, HB7130-2, Size / quantity:
16T308/50****Order data**

Order number	GG2656 16T308/50
GTIN	4067263096924
Item class	GGN

Technical description

Cutting speed v_c main application	100 - 170 mm/min
Contents	260988 HB7130-2
Feed f	0.2 - 0.3 mm/rev.
Cutting depth a_p	0.55 - 4 mm
Quantity	50
ISO code indexable insert	TCMT16T308
Grade	HB7130-2
Chip breaker	VM
Type of product	Indexable insert for turning

Accessories

TCMT 16T308 Grade HB7130-2

260988 HB7130-2