

**Value pack turning insert medium machining VCMT, Size / quantity:  
160408/30****Order data**

Order number	GG2667 160408/30
GTIN	4067263097310
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.55 - 2.5 mm
Cutting speed $v_c$ main application	80 - 135 mm/min
Contents	261476 HBT130
Feed $f$	0.2 - 0.3 mm/rev.
Quantity	30
ISO code indexable insert	VCMT160408
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

---

## Accessories

VCMT 160408 Grade HBT130

261476 HBT130