

**Turning insert, medium machining VBMT, HBT130, Size / quantity: 160408/30****Order data**

Order number	GG2663 160408/30
GTIN	4067263097099
Item class	GGN

Technical description

Feed f	0.2 - 0.3 mm/rev.
Cutting depth a_p	0.55 - 2.5 mm
Cutting speed v_c main application	80 - 135 mm/min
Contents	261259 HBT130
Quantity	30
ISO code indexable insert	VBMT160408
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

VBMT 160408 Grade HBT130

261259 HBT130