

**Turning insert, medium machining VBMT, HBT130, Size / quantity: 160404/50****Order data**

Order number	GG2663 160404/50
GTIN	4067263097082
Item class	GGN

Technical description

Cutting depth a_p	0.25 - 2.5 mm
Contents	261257 HBT130
Feed f	0.2 - 0.3 mm/rev.
Cutting speed v_c main application	80 - 135 mm/min
Quantity	50
ISO code indexable insert	VBMT160404
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

VBMT 160404 Grade HBT130

261257 HBT130