


HOLEX
HOLEX Pro Inox solid carbide high-performance drill, plain shank DIN 6535 HA, AlTiN, Ø DC m7: 11,2mm

Order data

Order number	GG2685 11,2
GTIN	4067263087960
Item class	GGN

Description
Version:

Efficient drilling especially for use in **stainless and acid-resistant steels**.

Straight main cutting edges with **optimised cutting edge design** for improved chip breaking behaviour. Enlarged flutes for **excellent chip evacuation**. Increased wear resistance due to **improved carbide substrate** and **high temperature resistant coating**.

Same as number. 122685.

Form HB available with No. GG 1286 at the same price. Form HB only available from $\geq \varnothing 3$ mm.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Contents	5
Standard	DIN 6537
Flute length L_c	71 mm
Nominal $\varnothing D_c$	11.2 mm
Shank $\varnothing D_s$	12 mm

Number of cutting edges Z	2
recommended maximum drilling depth L ₂	54.2 mm
Feed f in stainless steel < 900 N/mm ²	0.13 mm/rev.
Overall length L	118 mm
Tolerance nominal Ø	m7
Series	Pro Inox
Coating	AlTiN
Tool material	Solid carbide
Version	6×D
Point angle	140 degrees
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Colour ring	blue
Type of product	Twist Drill

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions		
Alu > 10% Si	suitable only under restricted conditions		
Steel < 500 N/mm ²	suitable		
Steel < 750 N/mm ²	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1100 N/mm ²	suitable		
INOX < 900 N/mm ²	suitable		
INOX > 900 N/mm ²	suitable		
Ti > 850 N/mm ²	suitable		
wet maximum	suitable		

wet minimum

suitable only under
restricted conditions

Accessories

HOLEX Pro Inox solid carbide high-performance drill, plain
shankDIN 6535 HA Ø DC m7 11,2 mm

122685 11,2