

Garant

**Value pack turning insert medium machining VCMT, Size / quantity:
160408/50**

**Order data**

Order number	GG2664 160408/50
GTIN	4067263097266
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 2.5 mm
Feed f	0.2 - 0.4 mm/rev.
Cutting speed v_c main application	100 - 170 mm/min
Contents	261459 HB7130-2
Quantity	50
ISO code indexable insert	VCMT160408
Grade	HB7130-2
Chip breaker	VM
Type of product	Indexable insert for turning

Accessories

VC.T 160408 Grade HB7130-2

261459 HB7130-2