

**Garant**
**T-slot cutter, Weldon shank,  $\varnothing D$  / Zeff: 21/1mm**


## Order data

Order number	218300 21/1
GTIN	4045197608062
Item class	210

## Description

### Version:

End mill with clamping face and internal coolant supply. Deeply recessed at the cutting area to allow working in very deep slots. Anti-corrosion surface treatment.

### Application:

For slots to DIN 650.

### Note:

Coolant feed via the internal coolant supply is preferable in order to achieve optimum chip clearance. Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

## Technical description

suitable indexable insert	SP.T 060304
Overhang $L_1$	26 mm
Pack of insert screws	219840 (8IP; 1.2 Nm)
Number of effective inserts $Z_{\text{eff}}$	1
Shank $\varnothing D_s$ h6	16 mm
Overall length $L_{\text{tot}}$	76 mm
Collar $\varnothing d_1$	11 mm
Cutting edge $\varnothing D_c$	21 mm
Slot depth $a_p$	9 mm

Corner chamfer angle	90 degrees
Number of indexable inserts	2
Shank type	Weldon shank
Through-coolant	yes
Tool exchange	PowerCard
Type of product	Slot milling cutter

---

## Accessories

Set of insert screws 10 pieces	219840
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2