

**Turning insert, medium machining VCMT, HBT130, Size / quantity: 160404/30****Order data**

Order number	GG2667 160404/30
GTIN	4067263097297
Item class	GGN

Technical description

Contents	261474 HBT130
Feed f	0.2 - 0.3 mm/rev.
Cutting speed v_c main application	80 - 135 mm/min
Cutting depth a_p	0.25 - 2.5 mm
Quantity	30
ISO code indexable insert	VCMT160404
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

Accessories

VCMT 160404 Grade HBT130

261474 HBT130