

**Turning insert, medium machining VCMT, HBT130, Size / quantity: 110304/30****Order data**

Order number	GG2667 110304/30
GTIN	4067263097273
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	80 - 135 mm/min
Cutting depth $a_p$	0.25 - 1.75 mm
Contents	261472 HBT130
Feed $f$	0.2 - 0.3 mm/rev.
Quantity	30
ISO code indexable insert	VCMT110304
Grade	HBT130
Chip breaker	MM
Type of product	Indexable insert for turning

## Accessories

VCMT 110304 Grade HBT130

261472 HBT130