

Garant**Parting-off/grooving insert, HB7020, Groove width w (mm) / quantity: 2/50****Order data**

Order number	GG2736 2/50
GTIN	4067263097198
Item class	GGN

Description**Version:**Chip beaker for small \varnothing and reduction in cutting forces.**Technical description**

Corner radius R	0.2 mm
Tolerance groove width w	± 0.03 mm
Quantity	50
Feed f	0.05 - 0.15 mm/rev.
Contents	273701 2
Grade	HB7020
Main application	P
Secondary application	M
Type of product	Indexable insert for grooving

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	220 m/min	P
Steel < 750 N/mm ²	suitable	180 m/min	P
Steel < 900 N/mm ²	suitable	170 m/min	P
Steel < 1100 N/mm ²	suitable	140 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	120 m/min	P
INOX < 900 N/mm ²	suitable	140 m/min	M
INOX > 900 N/mm ²	suitable	130 m/min	M
Ti > 850 N/mm ²	suitable	60 m/min	S
GG(G)	suitable	200 m/min	K
CuZn	suitable	250 m/min	N
Uni	suitable		
continuous	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		

Accessories

Parting-off / grooving insert Groove width w 2 mm

273701 2