

Garant**Turning insert, medium machining CCGT, HB7310, Size / quantity: 09T304/50****Order data**

Order number	GG2671 09T304/50
GTIN	4067263097761
Item class	GGN

Technical description

Cutting depth a_p	0.25 - 3.25 mm
Contents	260150 HB7310
Cutting speed v_c main application	250 - 600 mm/min
Feed f	0.1 - 0.3 mm/rev.
Quantity	50
ISO code indexable insert	CCGT09T304
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

CC.T 09T304 Grade HB7310

260150 HB7310