

Garant**Turning insert, medium machining CCGT, HB7310, Size / quantity: 09T308/50****Order data**

Order number	GG2671 09T308/50
GTIN	4067263097785
Item class	GGN

Technical description

Cutting speed v_c main application	250 - 600 mm/min
Feed f	0.1 - 0.3 mm/rev.
Cutting depth a_p	0.55 - 3.25 mm
Contents	260152 HB7310
Quantity	50
ISO code indexable insert	CCGT09T308
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

CC.T 09T308 Grade HB7310

260152 HB7310