

Garant**Turning insert, medium machining CCGT, HU7310, Size / quantity: 120408/30****Order data**

Order number	GG2668 120408/30
GTIN	4067263097570
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 4.25 mm
Cutting speed v_c main application	350 - 600 mm/min
Contents	260160 HU7310
Feed f	0.1 - 0.3 mm/rev.
Quantity	30
ISO code indexable insert	CCGT120408
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

CC.T 120408 Grade HU7310

260160 HU7310