


Garant**Turning insert, medium machining CCGT, HU7310, Size / quantity: 09T308/50****Order data**

Order number	GG2668 09T308/50
GTIN	4067263097525
Item class	GGN

Technical description

Cutting speed v_c main application	350 - 600 mm/min
Feed f	0.1 - 0.3 mm/rev.
Contents	260152 HU7310
Cutting depth a_p	0.55 - 3.25 mm
Quantity	50
ISO code indexable insert	CCGT09T308
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

CC.T 09T308 Grade HU7310

260152 HU7310