

Garant**Turning insert, medium machining CCGT, HU7310, Size / quantity: 09T302/50****Order data**

| | |
|--------------|------------------|
| Order number | GG2668 09T302/50 |
| GTIN | 4067263097389 |
| Item class | GGN |

Technical description

| | |
|--------------------------------------|------------------------------|
| Cutting depth a_p | 0.15 - 3.25 mm |
| Feed f | 0.1 - 0.3 mm/rev. |
| Quantity | 50 |
| Contents | 260148 HU7310 |
| Cutting speed v_c main application | 350 - 600 mm/min |
| ISO code indexable insert | CCGT09T302 |
| Grade | HU7310 |
| Chip breaker | AM |
| Type of product | Indexable insert for turning |

Accessories

CC.T 09T302 Grade HU7310

260148 HU7310