


Garant
Value pack GARANT Master Steel solid carbide mini milling cutter HPC, 5 pieces

Order data

Order number	GG2297 2,5
GTIN	4067263091820
Item class	GGN

Description
Version:

Extra short cutter for maximum stability. **Shank length to DIN** for improved support of the tool in the holder. This significantly increases the tool life.

Save the regrinding costs: It is cheaper to use a carbide mini milling cutter to the limit of wear and throw it away, than to regrind it.

Same as No. 202297.

Technical description

Tolerance nominal \varnothing	e8
Cutting edge $\varnothing D_c$	2.5 mm
Corner chamfer width at 45°	0.03 mm
Shank $\varnothing D_s$	6 mm
Helix angle	45 degrees
Direction of infeed	horizontal, oblique and vertical
Flute length L_c	5 mm

Feed f_z for side milling in steel < 900 N/mm ²	0.012 mm
Corner chamfer angle	45 degrees
Feed f_z for slot milling in steel < 900 N/mm ²	0.01 mm
Shank	DIN 6535 HB to h6
Contents	5
No. of teeth Z	3
Overall length L	50 mm
Shank form	HB
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Works standard
Type	N
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	0.5×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	290 m/min	N
Alu > 10% Si	suitable only under restricted conditions	240 m/min	N
Steel < 500 N/mm ²	suitable	140 m/min	P
Steel < 750 N/mm ²	suitable	120 m/min	P
Steel < 900 N/mm ²	suitable	100 m/min	P

Steel < 1100 N/mm ²	suitable	70 m/min	P
Steel < 1400 N/mm ²	suitable	50 m/min	P
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	70 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	40 m/min	S
GG(G)	suitable	85 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		

Accessories

GARANT Master Steel solid carbide mini milling cutterHPC
Ø e8 DC 2,5 mm

202295 2,5

GARANT Master Steel solid carbide mini-milling cutterHPC
Ø e8 DC 2,5 mm

202297 2,5