

Garant**Turning insert, medium machining CCGT, HB7310, Size / quantity: 09T302/30****Order data**

Order number	GG2671 09T302/30
GTIN	4067263097730
Item class	GGN

Technical description

Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	250 - 600 mm/min
Cutting depth a_p	0.15 - 3.25 mm
Contents	260148 HB7310
Quantity	30
ISO code indexable insert	CCGT09T302
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

CC.T 09T302 Grade HB7310

260148 HB7310