

Garant**Turning insert, medium machining CCGT, HB7310, Size / quantity: 120408/50****Order data**

Order number	GG2671 120408/50
GTIN	4067263097846
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 4.25 mm
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	250 - 600 mm/min
Contents	260160 HB7310
Quantity	50
ISO code indexable insert	CCGT120408
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

CC.T 120408 Grade HB7310

260160 HB7310