

Garant**Turning insert, medium machining CNMG, HB7020, Size / quantity: 120408/50****Order data**

Order number	GG2527 120408/50
GTIN	4067263092322
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 4.25 mm
Cutting speed v_c main application	130 - 280 mm/min
Feed f	0.25 - 0.4 mm/rev.
Quantity	50
Contents	250158 HB7020
ISO code indexable insert	CNMG120408
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

CNMG 120408 Grade HB7020

250158 HB7020