

Garant**Turning insert, medium machining CNMG, HB7020, Size / quantity: 190624/50****Order data**

Order number	GG2527 190624/50
GTIN	4067263092469
Item class	GGN

Technical description

Cutting speed v_c main application	130 - 280 mm/min
Feed f	0.25 - 0.4 mm/rev.
Cutting depth a_p	1.6 - 6.75 mm
Quantity	50
Contents	250176 HB7020
ISO code indexable insert	CNMG190624
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

Accessories

CNMG 190624 Grade HB7020

250176 HB7020