

Garant**Turning insert, medium machining CNMG, HB7020, Size / quantity: 190616/30****Order data**

| | |
|--------------|------------------|
| Order number | GG2527 190616/30 |
| GTIN | 4067263092438 |
| Item class | GGN |

Technical description

| | |
|--------------------------------------|------------------------------|
| Cutting speed v_c main application | 130 - 280 mm/min |
| Cutting depth a_p | 1.6 - 6.75 mm |
| Feed f | 0.25 - 0.4 mm/rev. |
| Contents | 250174 HB7020 |
| Quantity | 30 |
| ISO code indexable insert | CNMG190616 |
| Grade | HB7020 |
| Chip breaker | SM |
| Type of product | Indexable insert for turning |

Accessories

CNMG 190616 Grade HB7020

250174 HB7020