

**Garant****Turning insert, medium machining CNMG, HB7020, Size / quantity: 120408/30****Order data**

Order number	GG2527 120408/30
GTIN	4067263092315
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.55 - 4.25 mm
Cutting speed $v_c$ main application	130 - 280 mm/min
Contents	250158 HB7020
Feed $f$	0.25 - 0.4 mm/rev.
Quantity	30
ISO code indexable insert	CNMG120408
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

CNMG 120408 Grade HB7020

250158 HB7020