

**Garant****Turning insert, medium machining CNMG, HB7020, Size / quantity: 160612/30****Order data**

Order number	GG2527 160612/30
GTIN	4067263092391
Item class	GGN

**Technical description**

Cutting depth $a_p$	0.8 - 5.5 mm
Feed $f$	0.25 - 0.4 mm/rev.
Contents	250170 HB7020
Cutting speed $v_c$ main application	130 - 280 mm/min
Quantity	30
ISO code indexable insert	CNMG160612
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

## Accessories

CNMG 160612 Grade HB7020

250170 HB7020