

**Garant****Turning insert, roughing CNMG, HB7020, Size / quantity: 120412/30****Order data**

Order number	GG2531 120412/30
GTIN	4067263092599
Item class	GGN

**Technical description**

Contents	250324 HB7020
Cutting speed $v_c$ main application	100 - 260 mm/min
Feed $f$	0.3 - 0.5 mm/rev.
Cutting depth $a_p$	0.8 - 4.25 mm
Quantity	30
ISO code indexable insert	CNMG120412
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

## Accessories

CNMG 120412 Grade HB7020

250324 HB7020