

**Garant****Turning insert, medium machining DCGT, HU7310, Size / quantity: 11T308/30****Order data**

Order number	GG2672 11T308/30
GTIN	4067263098034
Item class	GGN

**Technical description**

Feed f	0.1 - 0.3 mm/rev.
Cutting depth $a_p$	0.55 - 2.75 mm
Contents	260464 HU7310
Cutting speed $v_c$ main application	350 - 600 mm/min
Quantity	30
ISO code indexable insert	DCGT11T308
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

## Accessories

DC.T 11T308 Grade HU7310

260464 HU7310