

Garant**Turning insert, roughing CNMG, HB7020, Size / quantity: 120408/30****Order data**

Order number	GG2531 120408/30
GTIN	4067263092575
Item class	GGN

Technical description

Contents	250322 HB7020
Cutting speed v_c main application	100 - 260 mm/min
Cutting depth a_p	0.55 - 4.25 mm
Feed f	0.3 - 0.5 mm/rev.
Quantity	30
ISO code indexable insert	CNMG120408
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

CNMG 120408 Grade HB7020

250322 HB7020