

**Garant****Turning insert, roughing CNMG, HB7020, Size / quantity: 120408/50****Order data**

Order number	GG2531 120408/50
GTIN	4067263092582
Item class	GGN

**Technical description**

Feed f	0.3 - 0.5 mm/rev.
Cutting depth $a_p$	0.55 - 4.25 mm
Cutting speed $v_c$ main application	100 - 260 mm/min
Quantity	50
Contents	250322 HB7020
ISO code indexable insert	CNMG120408
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

## Accessories

CNMG 120408 Grade HB7020

250322 HB7020