

Garant**Turning insert, medium machining DCGT, HU7310, Size / quantity: 11T304/50****Order data**

Order number	GG2672 11T304/50
GTIN	4067263098027
Item class	GGN

Technical description

Contents	260462 HU7310
Cutting depth a_p	0.25 - 2.75 mm
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	350 - 600 mm/min
Quantity	50
ISO code indexable insert	DCGT11T304
Grade	HU7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

DC.T 11T304 Grade HU7310

260462 HU7310