


**Turning insert, roughing CNMG, HBT020, Size / quantity: 160612/50****Order data**

Order number	GG2534 160612/50
GTIN	4067263092803
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	100 - 220 mm/min
Cutting depth $a_p$	0.8 - 5.5 mm
Feed $f$	0.3 - 0.5 mm/rev.
Quantity	50
Contents	250221 HBT020
ISO code indexable insert	CNMG160612
Grade	HBT020
Chip breaker	PR
Type of product	Indexable insert for turning

## Accessories

CNMG 160612 Grade HBT020

250221 HBT020