

**Garant**

**Turning insert, medium machining DNMG, HB7020, Size / quantity:  
110404/30**

**Order data**

Order number	GG2535 110404/30
GTIN	4067263092810
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	125 - 280 mm/min
Contents	250752 HB7020
Cutting depth $a_p$	0.25 - 2.75 mm
Feed $f$	0.25 - 0.4 mm/rev.
Quantity	30
ISO code indexable insert	DNMG110404
Grade	HB7020
Chip breaker	SM
Type of product	Indexable insert for turning

---

## Accessories

DNMG 110404 Grade HB7020

250752 HB7020