

Garant**Turning insert, medium machining SCGT, HB7310, Size / quantity: 09T304/30****Order data**

Order number	GG2679 09T304/30
GTIN	4067263098256
Item class	GGN

Technical description

Contents	260762 HB7310
Cutting depth a_p	0.25 - 3.25 mm
Feed f	0.1 - 0.3 mm/rev.
Cutting speed v_c main application	250 - 600 mm/min
Quantity	30
ISO code indexable insert	SCGT09T304
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

SC.T 09T304 Grade HB7310

260762 HB7310