

Garant**Turning insert, roughing CNMG, HB7020, Size / quantity: 190616/30****Order data**

Order number	GG2531 190616/30
GTIN	4067263092698
Item class	GGN

Technical description

Contents	250341 HB7020
Cutting depth a_p	1.6 - 6.75 mm
Cutting speed v_c main application	100 - 260 mm/min
Feed f	0.3 - 0.5 mm/rev.
Quantity	30
ISO code indexable insert	CNMG190616
Grade	HB7020
Chip breaker	SG
Type of product	Indexable insert for turning

Accessories

CNMG 190616 Grade HB7020

250341 HB7020