

Garant**Turning insert, medium machining DCGT, HB7310, Size / quantity: 11T302/50****Order data**

Order number	GG2675 11T302/50
GTIN	4067263098102
Item class	GGN

Technical description

Cutting depth a_p	0.15 - 2.75 mm
Cutting speed v_c main application	250 - 600 mm/min
Contents	260458 HB7310
Feed f	0.1 - 0.3 mm/rev.
Quantity	50
ISO code indexable insert	DCGT11T302
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

DC.T 11T302 Grade HB7310

260458 HB7310