

**Garant****Turning insert, medium machining SCGT, HB7310, Size / quantity: 09T302/50****Order data**

Order number	GG2679 09T302/50
GTIN	4067263098249
Item class	GGN

**Technical description**

Cutting speed $v_c$ main application	250 - 600 mm/min
Cutting depth $a_p$	0.15 - 3.25 mm
Contents	260761 HB7310
Feed $f$	0.1 - 0.3 mm/rev.
Quantity	50
ISO code indexable insert	SCGT09T302
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

**Accessories**

SCGT 09T302 Grade HB7310

260761 HB7310