



**Turning insert, medium machining DNMG, HBT020, Size / quantity:  
110408/50**



### Order data

Order number	GG2538 110408/50
GTIN	4067263092940
Item class	GGN

### Technical description

Feed f	0.2 - 0.3 mm/rev.
Cutting depth $a_p$	0.55 - 2.75 mm
Cutting speed $v_c$ main application	120 - 240 mm/min
Quantity	50
Contents	250781 HBT020
ISO code indexable insert	DNMG110408
Grade	HBT020
Chip breaker	PM
Type of product	Indexable insert for turning

---

## Accessories

DNMG 110408 Grade HBT020

250781 HBT020