

Garant**Turning insert, medium machining DCGT, HB7310, Size / quantity: 11T308/50****Order data**

Order number	GG2675 11T308/50
GTIN	4067263098140
Item class	GGN

Technical description

Cutting depth a_p	0.55 - 2.75 mm
Contents	260464 HB7310
Cutting speed v_c main application	250 - 600 mm/min
Feed f	0.1 - 0.3 mm/rev.
Quantity	50
ISO code indexable insert	DCGT11T308
Grade	HB7310
Chip breaker	AM
Type of product	Indexable insert for turning

Accessories

DC.T 11T308 Grade HB7310

260464 HB7310